


SW 32 Ti

6 x 38.5 mL

SW 32 Ti



Swinging-Bucket Rotor and Buckets, Titanium

For use in instruments classified: **H R S**

Major applications: Separation of subcellular particles and viruses in density gradients.

Max. RPM	Max. g	k Factor	Number of Tubes Volume/Size	Rotor Capacity
32 000	175 000	204	6 x 38.5 mL 1 x 3.5 in 25 x 89 mm	231 mL

No. 369694. SW 32 Ti Rotor Package with 1 box 326823 Polyallomer Tubes, 2 boxes 344058 Ultra-Clear™ Tubes, 1 box 355631 Polycarbonate Tubes, 331186 Bucket Holder Rack, 306812 Spinkote™ Lubricant, 335148 Vacuum Grease, 335456 Overspeed Disk, and 812715 O-rings, and 978358 hooked O-ring Removal Tool.

No. 369650. SW 32 Ti Rotor Assembly.

Tubes

Tube Style/Material	Vol. (mL) <i>g-Max</i>	Part No.	Quantity	Size (mm)	Floating Spacers (qty. 1)	Adapters (qty. 1)	g-Force	k Factor	Max. Speed
OptiSeal Polyallomer	32.4	361625	56	25 x 77	392833*	—	175 000	155	32 000
Quick-Seal®	15.0	343664	50	25 x 38	355536	—	175 000	81	32 000
Polyallomer	27.0	343665	50	25 x 64	355536	—	175 000	146	32 000
Bell-Top	33.5	344623	50	25 x 83	355536	—	175 000	192	32 000
Quick-Seal	8.4	358652	50	25 x 38	355536	358156**	175 000	74	32 000
Konical™	22.5	358654	50	25 x 76	355536	358156**	175 000	155	32 000
Polyallomer	28.0	358651	50	25 x 83	355536	358156**	175 000	198	32 000
Bell-Top									
Konical	25.5	358125	50	25 x 76	—	358156**	175 000	156	32 000
Polyallomer	31.5	358126	50	25 x 89	—	358156**	175 000	156	32 000
Thickwall	31.0	355642	25	25 x 89	—	—	175 000	198	32 000
Polyallomer									
Thinwall	38.5	326823	50	25 x 89	—	—	175 000	204	32 000
Polyallomer									
Thickwall	31.0	355631	25	25 x 89	—	—	175 000	202	32 000
Polycarbonate									
Ultra-Clear™	38.5	344058	50	25 x 89	—	—	175 000	204	32 000

* Set of 2.

** Package of 6.

Note: To help you locate g-Max tubes in the rotor listings, these tubes are highlighted with bold, italic type.

Rotor Replacement Parts

335456 Overspeed Disk, 32 000 rpm
332400 Rotor Stand
369692 Bucket Set, with Caps and O-rings, set of 6
812715 O-ring for Bucket

Extra Buckets for the SW 32 Ti

The buckets of the SW 32.1 can be used with the SW 32 rotor head.
369693 Bucket Set, with Caps and O-rings, set of 6

Adapters/Spacers

355536 358156 361669

